



GC Valves potable water solenoid valve, 2-port (2-way), 2-position, N.C., 316 stainless steel body, EPDM rubber seal(s), 2in female NPT inlet(s), 2in female NPT outlet(s), Cv=13, 24 VDC operating voltage, 10W, NSF/ANSI/CAN 61.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/NS211YH16C7JJ2>

Technical Specifications

Brand	GC Valves
Item	Valve
Working Fluid	Potable water
Valve Type	Solenoid process
Port Quantity	2-port (2-way)
Number Of Positions	2
Valve Configuration	N.C.
Action	Single solenoid spring return
Body Material	316 stainless steel
Seal Material	EPDM rubber

Inlet Port	2in female NPT
Outlet Port	2in female NPT
Flow Coefficient	13
Minimum Operating Pressure	5 psi
Maximum Operating Pressure	150 psi
Working Fluid Temperature	32–176 °F
Operating Voltage	24 VDC
Power Rating	10W
Electrical Connection	18mm DIN style wiring plug
Potable Water Certifications	NSF/ANSI/CAN 61

Agency Approvals

UL Listed File #	None
UL Recognized File #	YSYI2 - MH17997
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LR69111
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	NSF Listing

Dimensional Drawings



2D Drawing PDF Link:
[https://cdn.automationdirect.com
/static/drawings/2d/NS211YH16C7JJ2.pdf](https://cdn.automationdirect.com/static/drawings/2d/NS211YH16C7JJ2.pdf)
See store item page for other formats.