

HN0221S0307 Cut Sheet



CCEA Herionova series LED light bar, 329mm length, 24 VDC operating voltage, daylight white, bracket mount, pigtail, anodized aluminum body, 9.8ft/3m cable length, IP67. Mounting bracket included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HN0221S0307>

Technical Specifications

Brand	CCEA
Item	LED light bar
Series	Herionova
Length	329mm
Operating Voltage	24 VDC
LED Color	Daylight white
Color Temperature	5000K
Mounting	Bracket
Connection	Pigtail
Power Consumption	26.5W
Body Material	Anodized aluminum
Cable Length	9.8ft/3m
IP Rating	IP67
Includes	Mounting bracket

Agency Approvals

UL Listed File #	None
UL Recognized File #	E506617
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/HN0221S0307.pdf>
See store item page for other formats.