


# HPX1-BB3P-2SP Cut Sheet



IronHorse busbar, 64A, 600 VAC, cut to length not permitted, connects up to 2 HMMP-32H Manual motor protectors without accessories. Use HPX1-PTB-MP power terminal to connect feeder.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HPX1-BB3P-2SP>

## Technical Specifications

|                        |   |
|------------------------|---|
| <b>Brand</b>           | IronHorse   |
| <b>Item</b>            | Busbar  |
| <b>Amperage Rating</b> | 64A   |
| <b>Voltage Rating</b>  | 600 VAC   |
| <b>Cut to Length</b>   | Not permitted   |
| <b>Application</b>     | Connects up to 2 HMMP-32H Manual motor protectors without accessories. Use HPX1-PTB-MP power terminal to connect feeder |

## Agency Approvals

|                         |  |
|-------------------------|--|
| <b>UL Listed File #</b> | E195426                                |
| <b>CE</b>               | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>       | None                                   |
| <b>RoHS Status</b>      | Yes (See CE Doc)                       |
| <b>EU REACH</b>         | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/HPX1-BB3P-2SP.pdf>  
See store item page for other formats.