

# HPX1-PTBE-MP Cut Sheet



IronHorse incoming power terminal block, 3-pole, 64A, 12-4 AWG. For use with HMMP-32H manual motor protectors. Required when using a HMMP-32H in a UL Type E application.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HPX1-PTBE-MP>

## Technical Specifications

<b>Brand</b>	IronHorse
<b>Terminal Block Type</b>	Incoming power
<b>Item</b>	Terminal block
<b>Number of Poles</b>	3
<b>Amperage Rating</b>	64A
<b>Conductor Size</b>	12-4 AWG
<b>For Use With</b>	HMMP-32H manual motor protectors
<b>Application</b>	Required when using a HMMP-32H in a UL Type E application

## Agency Approvals

<b>UL Listed File #</b>	E195426
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/HPX1-PTBE-MP.pdf>  
See store item page for other formats.