

# HUM-R-20 Cut Sheet



ProSense temperature/humidity sensor, room sensor, plastic wall mounting subplate process connection, Output: 2-channel, current, -19.9 to +60 °C, 0 to 99.9% RH, IP10, wall mount, screw terminals.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HUM-R-20>

## Technical Specifications

<b>Brand</b>	ProSense
<b>Item</b>	Temperature/humidity sensor
<b>Sensor Type</b>	Room sensor
<b>Media Type</b>	Air
<b>Process Connection</b>	Plastic wall mounting subplate
<b>Number Of Output Channels</b>	2
<b>Output</b>	Current
<b>Output</b>	4–20 mA

<b>Output 2</b>	4–20 mA
<b>Temperature Sensing Range</b>	-19.9 to +60 °C
<b>Humidity Sensing Range</b>	0 to 99.9% RH
<b>Operating Voltage</b>	24 VDC
<b>IP Rating</b>	IP10
<b>Housing Material</b>	Plastic
<b>Mounting</b>	Wall
<b>Electrical Connection</b>	Screw terminals

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/HUM-R-20.pdf>  
See store item page for other formats.