

HUM-W-RS485 Cut Sheet



AchieVe temperature/humidity sensor, room sensor, plastic wall mounting subplate process connection, 1 port, Modbus, -40 to +80 °C, 0 to 100% RH, IP67, wall mount, push-in terminals.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HUM-W-RS485>

Technical Specifications

Brand	AchieVe
Item	Temperature/humidity sensor
Sensor Type	Room sensor
Media Type	Air
Process Connection	Plastic wall mounting subplate
Number of Ports	1
Output	Modbus
Communication Port and Connection Type(s)	(1) RS-485 (2-pin terminal)
Port Protocol(s)	Modbus RTU Slave

Port Speed(s)	up to 57.6k baud
Temperature Sensing Range	-40 to +80 °C
Humidity Sensing Range	0 to 100% RH
Operating Voltage	9-36 VDC
IP Rating	IP67
Housing Material	Plastic
Mounting	Wall
Electrical Connection	Push-in terminals

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/HUM-W-RS485.pdf>
See store item page for other formats.