

# IHS22 Cut Sheet



MK Morse hole saw, 1-3/8in (35mm), bi-metal cobalt, hardened steel backer, straight pitch, 1/8in (3.2mm) maximum cutting depth.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/IHS22>

## Technical Specifications

Brand	MK Morse	Tooth Density	8 teeth/in
Item	Hole saw	Toothing	Straight pitch
Hole Saw Size	1-3/8in (35mm)	Cutting Direction	Right hand
Maximum Cutting Depth	1/8in (3.2mm)	For Use On	Sheet metal
Material	Bi-metal cobalt	Application	Hole cutting
Hardened Steel Backer	Yes	Additional Information	Integrated spring for quick slug removal

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	<a href="#">View EU REACH document</a>
Other	<a href="#">RoHS Statement</a>