

ISWE-M18MP-NSS-A0 Cut Sheet



Contrinex inductive proximity sensor, tubular, 18 mm diameter x 63.5 mm body, chrome-plated brass housing, PNP, N.O. output, 8 mm sensing distance, semi-flush, 500 Hz switching frequency, IP67, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ISWE-M18MP-NSS-A0>

Technical Specifications

Brand	Contrinex	Repeatability	±0.006 mm
Item	Proximity sensor	Operating Voltage	10–30 VDC
Sensor Type	Inductive	Operating Temperature	-25 to +70 °C
Application	Standard duty, IO-Link and smart output	Weld Field Immune	No
Shape	Tubular	Chip Immune	No
Housing Size	18 mm diameter x 63.5 mm body	IP Rating	IP67
Housing Material	Chrome-plated brass	Connection	4-pin M12 quick-disconnect
Barrel Type	Threaded	IO-Link Compatible	Yes
Sensing Method	Extended sensing	Communication Port and Connection Type(s)	(1) 4-pin M12 A-coded (IO-Link) port(s)
Adjustable	Yes	Port Protocol(s)	IO-Link Class A Device
Number of Wires	4	Port Speed(s)	IO-Link COM2
Switching Output	PNP	IO-Link Version	IO-Link v1.1.3
Operation Mode	N.O. output	Standard I/O Mode Supported	Yes
Sensing Distance	8 mm	Includes	Mounting hardware
Mounting Type	Semi-flush	Additional Information	Purchase cable separately
Switching Frequency	500 Hz		

Agency Approvals

UL Listed File #	NRKH.E239373
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/ISWE-M18MP-NSS-A0.pdf>
See store item page for other formats.