

L7CA004U-AD Cut Sheet



LS Electric servo drive, 400W, 230 VAC, 1-phase, (1) RS-422/RS-485 (CN1) port(s), Modbus RTU. For use with 100W-400W systems.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/L7CA004U-AD>

Technical Specifications

Brand	LS Electric
Item	Servo drive
Voltage Type	AC
Amperage Rating	3.6A
Power Rating	400W
Nominal Input Voltage	230 VAC
Number of Input Phases	1
Output Type	SVPWM output
Steps per Revolution	Up to 17-bit (131072 ppr)
Encoder Output	Yes
Encoder Resolution	17-bit (131072 ppr)
Communication Port and Connection Type(s)	(1) RS-422/RS-485 (CN1)
Port Protocol(s)	Modbus RTU Slave
Port Speed(s)	up to 57.6k baud
Temperature Rating	0 to 50 deg C
Enclosure Type	Enclosed
IP Rating	IP20
Mounting	Panel
Control Mode	Torque, velocity and position
Command Signal(s)	<ul style="list-style-type: none">• step and direction• CW/CCW• A/B Quad• internal indexing (via discrete input and communication port)• torque and velocity (via analog input)
Number of Discrete Input Points	10
Discrete Input Type	Sinking/sourcing
Number of Discrete Output Points	8
Discrete Output Type	Sinking/sourcing
Number of Analog Input Channels	2
Analog Input Signal Type	Voltage

Input Voltage Signal Range	+/- 10 VDC
Tuning Mode	On-line auto/off-line auto/manual
Protection Type(s)	<ul style="list-style-type: none">• overcurrent• overvoltage• undervoltage• over-temperature• overload• encoder error• position error• current sensing error
Configuration	Software and keypad
For Use With	100W-400W systems

L7CA004U-AD Cut Sheet

Agency Approvals

UL Listed File #	E479434
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	RoHS Statement