

LC09-1004 Cut Sheet



Flowline Strobe Alert flashing alarm beacon, polycarbonate, NEMA 4X, 5in 22 AWG lead wires, 12-36 VDC operating voltage. For use with Flowline Switch-Tek series.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LC09-1004>

Technical Specifications

Brand	Flowline
Series	Strobe Alert
Item	Flashing alarm beacon
Flash Rate	1 per second
Material	Polycarbonate
NEMA Rating	4X
Electrical Connection	5in 22 AWG lead wires
Operating Voltage	12-36 VDC
For Use With	Flowline Switch-Tek series
Includes	Amber Xenon tube strobe

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/LC09-1004.pdf>
See store item page for other formats.