

LC40-1001 Cut Sheet



Flowline Switch-Pro remote level controller, tank fill, drain or alarm, (1) level switch input, (1) SPDT non-latching relay, adjustable time delay output, 120/240 VAC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LC40-1001>

Technical Specifications

Brand	Flowline
Series	Switch-Pro
Item	Remote level controller
Application	Single level switch automatic tank fill or drain, or high level alarm or low level alarm
Input	(1) level switch
Output	(1) SPDT non-latching relay, adjustable time delay
Operating Voltage	120/240 VAC
Indicating Type	LED indicators for level switch, power and relay status
Mounting	35mm DIN rail or through panel
Additional Information	Order level switch separately

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	YES
RoHS Status	No
EU REACH	View EU REACH document