

# LC42-1001 Cut Sheet



Flowline Switch-Pro remote level controller, tank fill or drain and alarm, (3) level switch input, (1) SPDT non-latching relay, (1) SPDT latching relay, adjustable time delay output, 120/240 VAC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LC42-1001>

## Technical Specifications

<b>Brand</b>	Flowline
<b>Series</b>	Switch-Pro
<b>Item</b>	Remote level controller
<b>Application</b>	Dual level switch automatic tank fill or drain, and single level switch high level alarm or low level alarm
<b>Input</b>	(3) level switch
<b>Output</b>	(1) SPDT non-latching relay, (1) SPDT latching relay, adjustable time delay
<b>Operating Voltage</b>	120/240 VAC
<b>Indicating Type</b>	LED indicators for level switch, power and relay status
<b>Mounting</b>	35mm DIN rail or through panel
<b>Additional Information</b>	Order level switches separately

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CSA File #</b>	1845008 (LR79326)
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>