

LH5946-PC-115-40 Cut Sheet



Dold safety relay, motor standstill monitoring, 0.2-4V, 2-channel, 115 VAC, (3) N.O. and (1) N.C. safety output(s), push-in cage clamp.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LH5946-PC-115-40>

Technical Specifications

Brand	Dold
Item	Safety relay
Relay Type	Motor standstill monitoring
Monitoring Circuit	0.2-4V
Number Of Channels	2
Control Voltage	115 VAC
Restart Type	Manual or automatic restart
Safety Output Type	(3) N.O. and (1) N.C.
Connection	Push-in cage clamp
Additional Information	(2) redundant measuring channels used for L2-L1 and L3-L1

Agency Approvals

UL Listed File #	E107778
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/LH5946-PC-115-40.pdf>
See store item page for other formats.