

PD1-AN-1A Cut Sheet



AutomationDirect inductive proximity sensor, tubular, 5mm diameter x 25mm body, stainless steel housing, NPN, N.O. output, 0.8mm sensing distance, flush, 5 kHz switching frequency, IP67, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PD1-AN-1A>

Technical Specifications

Brand	AutomationDirect	Sensing Distance	0.8mm
Item	Proximity sensor	Mounting Type	Flush
Sensor Type	Inductive	IO-Link Compatible	No
Application	Standard duty	Switching Frequency	5 kHz
Shape	Tubular	Operating Voltage	10-30 VDC
Housing Size	5mm diameter x 25mm body	Operating Temperature	-25 to 70c
Housing Material	Stainless steel	Weld Field Immune	No
Barrel Type	Threaded	Chip Immune	No
Sensing Method	Standard sensing	IP Rating	IP67
Adjustable	No	Connection	Pigtail
Number of Wires	3	Conductor Size	26 AWG
Switching Output	NPN	Cable Length	6.5ft/2m
Operation Mode	N.O. output	Includes	Mounting hardware

Agency Approvals

UL Listed File #	E328811
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document