

# PH1000MLI Cut Sheet



Hammond control transformer, encapsulated core, 1 kVA, 1-phase, 240/480 VAC primary, 25/120 VAC secondary, 50/60 Hz, panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PH1000MLI>

---

## Technical Specifications

<b>Brand</b>	Hammond
<b>Series</b>	Imperator
<b>Item</b>	Transformer
<b>Transformer Type</b>	Control
<b>Core Type</b>	Encapsulated
<b>Power Rating</b>	1 kVA
<b>Number of Phases</b>	1
<b>Primary Voltage</b>	240/480 VAC
<b>Secondary Voltage</b>	25/120 VAC
<b>Frequency</b>	50/60 Hz
<b>Electrostatic Shield</b>	No
<b>Mounting</b>	Panel

---

## Agency Approvals

<b>UL Listed File #</b>	E50394
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	LR 3902
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>