

MS25-1600 Cut Sheet



AutomationDirect MS25 series manual motor protector, pushbutton, 16A, thermal overload, 10.0-16.0A adjustable, 160A instantaneous trip rating, open, 45mm frame.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MS25-1600>

Technical Specifications

Brand	AutomationDirect
Series	MS25
Item	Motor protector
Starter Type	Manual
Actuator Type	Pushbutton
Amperage Rating	16A
Voltage Rating	600 VAC
Horsepower Rating	10hp
Relay Type	Thermal overload
Operation Type	Bi-metallic
Full Load Amperage Range	10.0-16.0A adjustable
Instantaneous Trip Rating	160A

Number of Poles	3
Power Poles	(3) N.O.
Trip Class	Trip Class 10
Phase Loss Sensitive	Yes
Ground Fault Protection	No
SCCR Rating	5kA SCCR
UL Rating	UL 508 rated
Enclosure Type	Open
Frame	45mm
Mounting	35mm DIN rail or panel
Connection	Screw terminal

Agency Approvals

UL Listed File #	E195426
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document