

# PLTC3-20-1TS-1 Cut Sheet



Quabbin instrumentation cable, overall shielded, PLTC and ITC, 300V, 1 twisted triad, 20 AWG, PVC conductor insulation material, black, white and red, PVC jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PLTC3-20-1TS-1>

## Technical Specifications

<b>Brand</b>	Quabbin
<b>Item</b>	Cable
<b>Wire/Cable Type</b>	Instrumentation
<b>UL Wire/Cable Type</b>	PLTC and ITC
<b>Applicable Standards</b>	UL 2250, UL 1685 and UL 13
<b>Application</b>	General purpose
<b>Flexibility</b>	Semi-flexible
<b>Voltage Rating</b>	300V
<b>Conductors</b>	1 twisted triad
<b>Conductor Size</b>	20 AWG
<b>Conductor Stranding</b>	10-stranded
<b>Conductor Material</b>	Bare copper
<b>Conductor Insulation Material</b>	PVC
<b>Conductor Insulation Color</b>	Black, white and red

<b>Shielding</b>	Overall shielded
<b>Jacket Material</b>	PVC
<b>Jacket Color</b>	Black
<b>Nominal Overall Cable Diameter</b>	0.212in
<b>Bulk Length</b>	Cut to length
<b>Package Type</b>	1 to 99ft = Coil, 100 to 798ft = 14 x 7in Reel, 799 to 872ft = 14 x 10in Reel, 873 to 1246ft = 16 x 10in Reel, 1247 to 1928ft = 18 x 10in Reel, 1929 to 2715ft = 18 x 13in Reel, 2716 to 3530ft = 24 x 17in Wooden Reel, 3531 to 7581ft = 30 x 17in Wooden Reel, 7582 to MAX = Large Wooden Reel

## Agency Approvals

<b>UL Listed File #</b>	E247880,E70148,E118830
<b>UL Recognized File #</b>	E69976
<b>UL Hazardous File #</b>	none
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>