

PSB60-REM40S Cut Sheet



RHINO redundancy module, 2 inputs, 24/48 VDC nominal input, 24-48 VDC output, 40A, alarm contact for operation monitoring, screw terminals, hazardous location rated. Requires (2) matched 24 or 48 VDC power supplies.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PSB60-REM40S>

Technical Specifications

| | |
|--|---|
| Brand | RHINO |
| Item | Redundancy module |
| Number of Inputs | 2 |
| Nominal Input Voltage | 24/48 VDC |
| Input voltage range | 24-48 VDC |
| Nominal Output Voltage | 24/48 VDC |
| Output Voltage Range | 24-48 VDC |
| Amperage Rating | 40A |
| Protection Type(s) | overcurrent |
| Alarm Contact for Operation Monitoring | Yes |
| Active Current Sharing | No |
| Housing Material | Metal |
| Mounting | 35mm DIN rail |
| Connector Type | Screw terminals |
| Application | Hazardous location rated |
| Requires | (2) matched 24 or 48 VDC power supplies |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | None |
| UL Recognized File # | E198298 & E197592 |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | 249074 |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |