

MTR2-P75-3BD36 Cut Sheet



IronHorse MTR standard efficiency AC induction motor, general purpose and inverter rated, 3/4hp, 3-phase, 230/460 VAC, 3600rpm, TEFC, 56C frame, rolled steel, C-face/removable rigid base mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MTR2-P75-3BD36>

Technical Specifications

Brand	IronHorse
Item	Motor
Series	MTR
Efficiency Group	Standard efficiency
Efficiency	71.5
Voltage Type	AC
Motor Type	Induction
Motor Application	General purpose and inverter rated
Horsepower Rating	3/4hp
Number of Phases	3
Voltage Rating	230/460 VAC
Synchronous Speed	3600rpm
Nameplate RPM	3450rpm
Overload Type	None
Enclosure Type	TEFC
Shaft Type	Round with square key

Shaft Diameter	5/8in
Shaft Material	1045 hot rolled (C-204) steel
Motor Frame	56C
Frame Material	Rolled steel
Electrically Reversible	Yes
Insulation Class	Class F
IP Rating	IP43
Constant Torque Rating	4:1
Variable Torque Rating	10:1
Service Factor	1.15
Integrated Brake	No
NEMA Design	Design B
Junction Box Orientation	F1
Mounting	C-face/removable rigid base
Mounting Orientation	Horizontal or vertical

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	256950
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document