

# PSM24-BFM600S Cut Sheet



RHINO buffer module, 1 input, 24 VDC nominal input, 22-28 VDC output, 25A, potentiometer, alarm contact for operation monitoring, removable screw terminals. Requires 24 VDC power supply.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PSM24-BFM600S>

## Technical Specifications

Brand	RHINO
Item	Buffer module
Number of Inputs	1
Nominal Input Voltage	24 VDC
Input voltage range	24 VDC
Nominal Output Voltage	24 VDC
Output Voltage Range	22-28 VDC
Amperage Rating	25A
Start Buffering Voltage Adjustment	Potentiometer
Buffer Time	200 msec hold-up at 25A or 4 seconds at 1.2A
Indicating Type	Dual color LED for status indication
Alarm Contact for Operation Monitoring	Yes
Remote On/Off	Yes
Housing Material	Metal
Mounting	35mm DIN rail
Connector Type	Removable screw terminals
Requires	24 VDC power supply

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>