


Q0190-1 Cut Sheet



Quabbin control and signal cable, unshielded, 3 conductors, 22 AWG, 7-stranded, tinned copper, PVC conductor insulation material, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/Q0190-1>

Technical Specifications

Brand	Quabbin
Item	Cable
Wire/Cable Type	Control and signal
UL Wire/Cable Type	PLTC, ITC and AWM
Applicable Standards	UL 2464
Application	General purpose
Flexibility	Semi-flexible
Voltage Rating	300V
Conductors	3 conductors
Conductor Size	22 AWG
Conductor Stranding	7-stranded
Conductor Material	Tinned copper
Conductor Insulation Material	PVC

Conductor Insulation Color	Black, white and red
Shielding	Unshielded
Jacket Material	PVC
Jacket Color	Gray
Nominal Overall Cable Diameter	0.209in
Bulk Length	Cut to length
Package Type	<ul style="list-style-type: none">• 20 to 99ft = Coil• 100 to 895ft = 14 x 7in Reel• 896 to 1275ft = 14 x 10in Reel• 1276 to 1955ft = 16 x 10in Reel• 1956 to 2735ft = 18 x 10in Reel• 2736 to 3555ft = 18 x 13in Reel• 3556 to 5000ft = 24 x 17in Wooden Reel

Agency Approvals

UL Listed File #	E247880, E69976, E70148
CSA File #	LL66965,LL51726
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement