


# Q4105-1 Cut Sheet



Quabbin control and signal cable, unshielded, 5 conductors, 18 AWG, 16-stranded, tinned copper, PVC conductor insulation material, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/Q4105-1>

## Technical Specifications

<b>Brand</b>	Quabbin	<b>Conductor Insulation Color</b>	Black, white, red, green and brown
<b>Item</b>	Cable	<b>Shielding</b>	Unshielded
<b>Wire/Cable Type</b>	Control and signal	<b>Jacket Material</b>	PVC
<b>UL Wire/Cable Type</b>	CM and AWM	<b>Jacket Color</b>	Gray
<b>Applicable Standards</b>	UL 2464	<b>Nominal Overall Cable Diameter</b>	0.272in
<b>Application</b>	General purpose	<b>Bulk Length</b>	Cut to length
<b>Flexibility</b>	Semi-flexible	<b>Package Type</b>	<ul style="list-style-type: none"><li>• 30 to 99ft = Coil</li><li>• 100 to 525ft = 14 x 7in Reel</li><li>• 526 to 755ft = 14 x 10in Reel</li><li>• 756 to 1155ft = 16 x 10in Reel</li><li>• 1156 to 1615ft = 18 x 10in Reel</li><li>• 1616 to 2100ft = 18 x 13in Reel</li><li>• 2101 to 4695ft = 24 x 17in Wooden Reel</li><li>• 4696 to 5000ft = 30 x 17in Wooden Reel</li></ul>
<b>Voltage Rating</b>	600V		
<b>Conductors</b>	5 conductors		
<b>Conductor Size</b>	18 AWG		
<b>Conductor Stranding</b>	16-stranded		
<b>Conductor Material</b>	Tinned copper		
<b>Conductor Insulation Material</b>	PVC		

## Agency Approvals

<b>UL Listed File #</b>	E118830
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	LL51726
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>