


Q5088-1 Cut Sheet



Quabbin Datamax continuous flexing Cat5e industrial Ethernet cable, shielded, 4 twisted pairs, 26 AWG, 7-stranded, tinned copper, HDPE conductor insulation material, TPE jacket, teal, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/Q5088-1>

Technical Specifications

| | |
|--------------------------------------|----------------------------------|
| Brand | Quabbin |
| Item | Cable |
| Series | Datamax |
| Protocol | Ethernet |
| Wire/Cable Type | Cat5e industrial Ethernet |
| UL Wire/Cable Type | CMX |
| Application | Data |
| Flexibility | Continuous flexing |
| Voltage Rating | 300V |
| Conductors | 4 twisted pairs |
| Conductor Size | 26 AWG |
| Conductor Stranding | 7-stranded |
| Conductor Material | Tinned copper |
| Conductor Insulation Material | High-density polyethylene (HDPE) |

| | |
|---------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Conductor Insulation Color | Pair 1: blue, white/blue, Pair 2: orange, white/orange, Pair 3: green, white/green and Pair 4: brown, white/brown |
| Shielding | Shielded |
| Jacket Material | TPE |
| Jacket Color | Teal |
| Nominal Overall Cable Diameter | 0.245in |
| Bulk Length | Cut to length |
| Package Type | <ul style="list-style-type: none">• 20 to 99ft = Coil• 100 to 650ft = 14 x 7in Reel• 651 to 930ft = 14 x 10in Reel• 931 to 1425ft = 16 x 10in Reel• 1426 to 1990ft = 18 x 10in Reel• 1991 to 2585ft = 18 x 13in Reel• 2586 to 4000ft = 24 x 17in Wooden Reel |

Agency Approvals

| | |
|-----------------------------|---------------------------------------------------------------------|
| UL Listed File # | E118830 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CSA File # | None |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |