


Q5752-1 Cut Sheet



Quabbin continuous flexing Cat5e industrial Ethernet cable, unshielded, 4 twisted pairs, 24 AWG, 7/32-stranded, tinned copper, HDPE conductor insulation material, FR-TPE jacket, teal, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/Q5752-1>

Technical Specifications

Brand	Quabbin
Item	Cable
Protocol	Ethernet
Wire/Cable Type	Cat5e industrial Ethernet
UL Wire/Cable Type	CMX and AWM
Applicable Standards	UL 2463
Application	Data
Flexibility	Continuous flexing
Voltage Rating	600V
Conductors	4 twisted pairs
Conductor Size	24 AWG
Conductor Stranding	7/32-stranded
Conductor Material	Tinned copper
Conductor Insulation Material	High-density polyethylene (HDPE)

Conductor Insulation Color	Pair 1: blue, white/blue, Pair 2: orange, white/orange, Pair 3: green, white/green and Pair 4: brown, white/brown
Shielding	Unshielded
Jacket Material	Flame retardant thermoplastic elastomer (FR-TPE) pressure extruded
Jacket Color	Teal
Nominal Overall Cable Diameter	0.248in
Bulk Length	Cut to length
Package Type	<ul style="list-style-type: none">• 20 to 99ft = Coil• 100 to 635ft = 14 x 7in Reel• 636 to 905ft = 14 x 10in Reel• 906 to 1390ft = 16 x 10in Reel• 1391 to 1940ft = 18 x 10in Reel• 1941 to 2525ft = 18 x 13in Reel• 2526 to 4500ft = 24 x 17in Wooden Reel

Agency Approvals

UL Listed File #	E118830
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement