


Q5922-1 Cut Sheet



Quabbin continuous flexing Cat6/6a industrial Ethernet cable, shielded, 4 twisted pairs, 24 AWG, 7-stranded, tinned copper, polyethylene conductor insulation material, TPE jacket, teal, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/Q5922-1>

Technical Specifications

Brand	Quabbin
Item	Cable
Protocol	Ethernet
Wire/Cable Type	Cat6/6a industrial Ethernet
UL Wire/Cable Type	CMX and AWM
Applicable Standards	UL 2463
Application	Data
Flexibility	Continuous flexing
Voltage Rating	600V
Conductors	4 twisted pairs
Conductor Size	24 AWG
Conductor Stranding	7-stranded
Conductor Material	Tinned copper
Conductor Insulation Material	Polyethylene
Conductor Insulation Color	Pair 1: blue, white/blue, Pair 2: orange, white/orange, Pair 3: green, white/green and Pair 4: brown, white/brown

Shielding	Shielded
Jacket Material	TPE
Jacket Color	Teal
Nominal Overall Cable Diameter	0.325in
Bulk Length	Cut to length
Package Type	1 to 75ft = Coil, 76 to 365ft = 14 x 7in Reel, 366 to 525ft = 14 x 10in Reel, 526 to 820ft = 16 x 10in Reel, 821 to 1150ft = 18 x 10in Reel, 1151 to 1500ft = 18 x 13in Reel, 1501 to 3215ft = 24 x 17in Wooden Reel, 3216 to 5280ft = 30 x 17in Wooden Reel, 5281 to MAX = Large Wooden Reel

Agency Approvals

UL Listed File #	E118830, E69976
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement