


Q5941-1 Cut Sheet



Quabbin Cat5e industrial Ethernet cable, unshielded, 4 twisted pairs, 22 AWG, solid, bare copper, polyethylene conductor insulation material, PVC jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/Q5941-1>

Technical Specifications

Brand	Quabbin	Shielding	Unshielded
Item	Cable	Jacket Material	PVC
Protocol	Ethernet	Jacket Color	Black
Wire/Cable Type	Cat5e industrial Ethernet	Nominal Overall Cable Diameter	0.267in
UL Wire/Cable Type	CMX and AWM	Bulk Length	Cut to length
Applicable Standards	UL 2463	Package Type	1 to 99ft = Coil, 100 to 505ft = 14 x 7in Reel, 506 to 545ft = 14 x 10in Reel, 546 to 775ft = 16 x 10in Reel, 776 to 1200ft = 18 x 10in Reel, 1201 to 1685ft = 18 x 13in Reel, 1686 to 2200ft = 24 x 17in Wooden Reel, 2201 to 4816ft = 30 x 17in Wooden Reel, 4817 to MAX = Large Wooden Reel
Application	Data		
Flexibility	Semi-flexible		
Voltage Rating	600V		
Conductors	4 twisted pairs		
Conductor Size	22 AWG		
Conductor Stranding	Solid		
Conductor Material	Bare copper		
Conductor Insulation Material	Polyethylene		
Conductor Insulation Color	Pair 1: blue, white/blue, Pair 2: orange, white/orange, Pair 3: green, white/green and Pair 4: brown, white/brown		

Agency Approvals

UL Listed File #	E118830, E70148, E69976
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement