

# Q6140-1 Cut Sheet



Quabbin control and signal cable, shielded, 2 conductors, 20 AWG, 7-stranded, tinned copper, PVC conductor insulation material, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/Q6140-1>

## Technical Specifications

<b>Brand</b>	Quabbin
<b>Item</b>	Cable
<b>Wire/Cable Type</b>	Control and signal
<b>UL Wire/Cable Type</b>	CM and AWM
<b>Applicable Standards</b>	UL 2092
<b>Application</b>	General purpose
<b>Flexibility</b>	Semi-flexible
<b>Voltage Rating</b>	300V
<b>Conductors</b>	2 conductors
<b>Conductor Size</b>	20 AWG
<b>Conductor Stranding</b>	7-stranded
<b>Conductor Material</b>	Tinned copper
<b>Conductor Insulation Material</b>	PVC

<b>Conductor Insulation Color</b>	Black and clear
<b>Shielding</b>	Shielded
<b>Jacket Material</b>	PVC
<b>Jacket Color</b>	Gray
<b>Nominal Overall Cable Diameter</b>	0.199in
<b>Bulk Length</b>	Cut to length
<b>Package Type</b>	<ul style="list-style-type: none"><li>• 30 to 99ft = Coil</li><li>• 100 to 985ft = 14 x 7in Reel</li><li>• 986 to 1405ft = 14 x 10in Reel</li><li>• 1406 to 2155ft = 16 x 10in Reel</li><li>• 2156 to 3015ft = 18 x 10in Reel</li><li>• 3016 to 3920ft = 18 x 13in Reel</li><li>• 3921 to 5000ft = 24 x 17in Wooden Reel</li></ul>

## Agency Approvals

<b>UL Listed File #</b>	E69976,E118830
<b>CE</b>	None
<b>CSA File #</b>	LL51726
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>