

Q6140-1 Cut Sheet



Quabbin control and signal cable, shielded, 2 conductors, 20 AWG, 7-stranded, tinned copper, PVC conductor insulation material, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/Q6140-1>

Technical Specifications

Brand	Quabbin
Item	Cable
Wire/Cable Type	Control and signal
UL Wire/Cable Type	CM and AWM
Applicable Standards	UL 2092
Application	General purpose
Flexibility	Semi-flexible
Voltage Rating	300V
Conductors	2 conductors
Conductor Size	20 AWG
Conductor Stranding	7-stranded
Conductor Material	Tinned copper
Conductor Insulation Material	PVC
Conductor Insulation Color	Black and clear

Shielding	Shielded
Jacket Material	PVC
Jacket Color	Gray
Nominal Overall Cable Diameter	0.199in
Bulk Length	Cut to length
Package Type	1 to 99ft = Coil, 100 to 989ft = 14 x 7in Reel, 990 to 1414ft = 14 x 10in Reel, 1415 to 2188ft = 16 x 10in Reel, 2189 to 3081ft = 18 x 10in Reel, 3082 to 4005ft = 18 x 13in Reel, 4006 to 8604ft = 24 x 17in Wooden Reel, 8605 to 14146ft = 30 x 17in Wooden Reel, 14147 to MAX = Large Wooden Reel

Agency Approvals

UL Listed File #	E69976,E118830
CE	None
CSA File #	LL51726
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement