

P1-M622-15DD2 Cut Sheet



Productivity1000 PLC, 24 VDC required, Ethernet, serial and USB C ports, battery backup, microSD card slot, Discrete Input: 8-point, DC, Discrete Output: 7-point, sourcing.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/P1-M622-15DD2>

Technical Specifications

Brand	Productivity1000	Voltage Type	DC
Item	PLC	Discrete Input Type	Sinking/sourcing
Total Memory	Up to 50 MB	Number of Non-Isolated Discrete Input Commons	1
Ladder Memory	Up to 50 MB	Number of Points per Discrete Input Common	8
User Data Memory	Up to 50 MB	Number of Discrete Output Points	7
Removable Media Type	MicroSD card slot	Nominal Output Voltage	12–24 VDC
Programming Language	Ladder	Discrete Output Type	Sourcing
Programming Software	Productivity Suite programming software v4.5 or later	Load Current	1 A/point
Communication Port and Connection Type(s)	• (2) Ethernet 10/100Base-T (RJ45) • (1) RS-232 (RJ12) • (1) RS-485 (4-pin terminal) • (1) USB C	Number of Non-Isolated Discrete Output Commons	1
Port Protocol(s)	• MQTT Client • MQTTs Client • Modbus RTU Master/Slave • Modbus TCP • ASCII In/out • TCP/IP • UDP/IP • EtherNet/IP explicit messaging scanner/adaptor • EtherNet/IP implicit messaging scanner/adaptor • Ethernet remote I/O • programming and monitoring • webserver (secure HTTPS)	Number of Points per Discrete Output Common	7
Port Speed(s)	• 10/100 Mbps • up to 115.2k baud	Maximum Number of PID Loops	100+ (configurable to memory limit)
Real Time Clock/Calendar	Yes	Includes	D2-BAT-1 battery
Retentive Memory	Yes	Requires	P2-RTB or P2-RTB-1 removable terminal block or ZIPLink pre-wired cables
Battery Backup	Yes	Dangerous Goods	• Battery Installed: No • Packaging Instructions: 969 • UN Number: UN3091 • Hazard Type: Lithium Batteries • Battery Type: Button • Lithium Content: 0.17 • Replacement Battery: D2-BAT-1 • Generic Battery: CR2354
Maximum Expansion Modules Allowed	4		
External Power Requirement	24 VDC		
Number of Discrete Input Points	8		
Nominal Input Voltage	12–24 VDC		

P1-M622-15DD2 Cut Sheet

Agency Approvals

UL Listed File #	E139594
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
[https://cdn.automationdirect.com
/static/drawings/2d/P1-M622-15DD2.pdf](https://cdn.automationdirect.com/static/drawings/2d/P1-M622-15DD2.pdf)
See store item page for other formats.
