


Q7125-1 Cut Sheet



Quabbin control and signal cable, unshielded, 4 conductors, 22 AWG, 7-stranded, tinned copper, PVC conductor insulation material, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/Q7125-1>

Technical Specifications

Brand	Quabbin	Shielding	Unshielded
Item	Cable	Jacket Material	PVC
Wire/Cable Type	Control and signal	Jacket Color	Gray
UL Wire/Cable Type	CM and AWM	Nominal Overall Cable Diameter	0.172in
Applicable Standards	UL 2464	Bulk Length	Cut to length
Application	General purpose	Package Type	1 to 99ft = Coil, 100 to 1325ft = 14 x 7in Reel, 1326 to 1892ft = 14 x 10in Reel, 1893 to 2929ft = 16 x 10in Reel, 2930 to 4124ft = 18 x 10in Reel, 4125 to 5362ft = 18 x 13in Reel, 5363 to 11517ft = 24 x 17in Wooden Reel, 11518 to 18935ft = 30 x 17in Wooden Reel, 18936 to MAX = Large Wooden Reel
Flexibility	Semi-flexible		
Voltage Rating	300V		
Conductors	4 conductors		
Conductor Size	22 AWG		
Conductor Stranding	7-stranded		
Conductor Material	Tinned copper		
Conductor Insulation Material	PVC		
Conductor Insulation Color	Black, white, red and green		

Agency Approvals

UL Listed File #	E69976,E118830
CE	None
CSA File #	LL51726
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement