


Q7165-1 Cut Sheet



Quabbin control and signal cable, unshielded, 15 conductors, 22 AWG, 7-stranded, tinned copper, PVC conductor insulation material, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/Q7165-1>

Technical Specifications

Brand	Quabbin	Shielding	Unshielded
Item	Cable	Jacket Material	PVC
Wire/Cable Type	Control and signal	Jacket Color	Gray
UL Wire/Cable Type	CM and AWM	Nominal Overall Cable Diameter	0.298in
Applicable Standards	UL 2464	Bulk Length	Cut to length
Application	General purpose	Package Type	1 to 99ft = Coil, 100 to 440ft = 14 x 7in Reel, 441 to 625ft = 14 x 10in Reel, 626 to 960ft = 16 x 10in Reel, 961 to 1345ft = 18 x 10in Reel, 1346 to 1750ft = 18 x 13in Reel, 1751 to 3910ft = 24 x 17in Wooden Reel, 3911 to 6255ft = 30 x 17in Wooden Reel, 6256 to MAX = Large Wooden Reel
Flexibility	Semi-flexible		
Voltage Rating	300V		
Conductors	15 conductors		
Conductor Size	22 AWG		
Conductor Stranding	7-stranded		
Conductor Material	Tinned copper		
Conductor Insulation Material	PVC		
Conductor Insulation Color	Color Code 1		

Agency Approvals

UL Listed File #	E118830, E69976
CSA File #	LL51726
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement