

PE532WHT100 Cut Sheet



HydroMode potable water tubing, polyethylene, white, 5/32in (4mm) outside diameter, 0.106in inside diameter, NSF/ANSI 61, 100ft package.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PE532WHT100>

Technical Specifications

Brand	HydroMode
Item	Tubing
Working Fluid	Potable water
Material	Polyethylene
Color	White
Outside Diameter	5/32in (4mm)
Inside Diameter	0.106in
Potable Water Certifications	NSF/ANSI 61
UV stabilized	No
Working Length	100ft package
Operating Pressure	75 psi
Operating Temperature	-50 to +140 deg F

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document