


# SAC-22-4U-1GY-1 Cut Sheet



AutomationDirect flexible sensor/actuator cable, unshielded, 4 conductors, 22 AWG, bare copper, PVC conductor insulation material, black, brown, blue and white, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SAC-22-4U-1GY-1>

## Technical Specifications

<b>Brand</b>	AutomationDirect	<b>Conductor Insulation Color</b>	Black, brown, blue and white
<b>Item</b>	Cable	<b>Shielding</b>	Unshielded
<b>Wire/Cable Type</b>	Sensor/actuator	<b>Jacket Material</b>	PVC
<b>UL Wire/Cable Type</b>	AWM	<b>Jacket Color</b>	Gray
<b>Applicable Standards</b>	UL 2464	<b>Nominal Overall Cable Diameter</b>	0.19in
<b>Application</b>	Sensor/actuator	<b>Bulk Length</b>	Cut to length
<b>Flexibility</b>	Flexible	<b>Package Type</b>	<ul style="list-style-type: none"><li>• 30 to 99ft = Coil</li><li>• 100 to 1080ft = 14 x 7in Reel</li><li>• 1081 to 1545ft = 14 x 10in Reel</li><li>• 1546 to 2365ft = 16 x 10in Reel</li><li>• 2366 to 3305ft = 18 x 10in Reel</li><li>• 3306 to 4300ft = 18 x 13in Reel</li><li>• 4301 to 5000ft = 24 x 17in Wooden Reel</li></ul>
<b>Voltage Rating</b>	300V		
<b>Conductors</b>	4 conductors		
<b>Conductor Size</b>	22 AWG		
<b>Conductor Stranding</b>	19-stranded		
<b>Conductor Material</b>	Bare copper		
<b>Conductor Insulation Material</b>	PVC		

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E505482
<b>UL Hazardous File #</b>	None
<b>CSA File #</b>	LL274638
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>