

# PGCN17-1005M Cut Sheet



SureGear precision planetary gearbox, 100:1 ratio, inline, 0.375in diameter output shaft, nominal output torque 5 N-m (44 lb-in), 2-stage, NEMA 17 frame. For use with SureStep NEMA 17 motors.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PGCN17-1005M>

## Technical Specifications

<b>Brand</b>	SureGear
<b>Item</b>	Gearbox
<b>Application</b>	Precision
<b>Gearbox Type</b>	Planetary
<b>Gear Ratio</b>	100:1
<b>Output Configuration</b>	Inline
<b>Gearbox Output Shaft Diameter</b>	0.375in
<b>Nominal Output Torque</b>	Nominal output torque 5 N-m (44 lb-in)
<b>Number of Stages</b>	2
<b>Frame</b>	NEMA 17
<b>For Use With</b>	SureStep NEMA 17 motors
<b>Includes</b>	Motor mounting hardware

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>