

SCE-HE24W120V Cut Sheet



Saginaw air-to-air heat exchanger, 43 W/deg C (24 W/deg F), 120 VAC operating voltage, 50/60 Hz, 1.80A running current, side mount, aluzinc coated steel, RAL 7035 light gray, textured powder coat finish. For use with NEMA/UL Type 3R & 12 enclosures.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-HE24W120V>

Technical Specifications

Brand	Saginaw
Item	Air-to-air Heat exchanger
Cooling Capacity	43 W/deg C (24 W/deg F)
Operating Voltage	120 VAC
Frequency	50/60 Hz
Running Current	1.80A
Mounting	Side
Housing Material	Aluzinc coated steel

Color	RAL 7035 light gray
Finish	Textured powder coat
For Use With	NEMA/UL Type 3R & 12 enclosures
Includes	Mounting template and hardware
Dangerous Goods	<ul style="list-style-type: none">• Packaging Instructions: 200• UN Number: 3159• Hazard Type: Compressed Gas

Agency Approvals

UL Listed File #	E498756
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SCE-HE24W120V.pdf>
See store item page for other formats.