


# PLTC3-20-4TSS-1 Cut Sheet



Quabbin instrumentation cable, individual and overall shielded, PLTC and ITC, 300V, 4 twisted triads, 20 AWG, PVC conductor insulation material, black, white and red, PVC jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PLTC3-20-4TSS-1>

## Technical Specifications

<b>Brand</b>	Quabbin
<b>Item</b>	Cable
<b>Wire/Cable Type</b>	Instrumentation
<b>UL Wire/Cable Type</b>	PLTC and ITC
<b>Applicable Standards</b>	UL 2250, UL 1685 and UL 13
<b>Application</b>	General purpose
<b>Flexibility</b>	Semi-flexible
<b>Voltage Rating</b>	300V
<b>Conductors</b>	4 twisted triads
<b>Conductor Size</b>	20 AWG
<b>Conductor Stranding</b>	10-stranded
<b>Conductor Material</b>	Bare copper
<b>Conductor Insulation Material</b>	PVC
<b>Conductor Insulation Color</b>	Black, white and red

<b>Shielding</b>	Individual and overall shielded
<b>Jacket Material</b>	PVC
<b>Jacket Color</b>	Black
<b>Nominal Overall Cable Diameter</b>	0.444in
<b>Bulk Length</b>	Cut to length
<b>Package Type</b>	<ul style="list-style-type: none"><li>• 20 to 50ft = Coil</li><li>• 51 to 200ft = 14 x 7in Reel</li><li>• 201 to 285ft = 14 x 10in Reel</li><li>• 286 to 435ft = 16 x 10in Reel</li><li>• 436 to 605ft = 18 x 10in Reel</li><li>• 606 to 785ft = 18 x 13in Reel</li><li>• 786 to 1760ft = 24 x 17in Wooden Reel</li><li>• 1761 to 2820ft = 30 x 17in Wooden Reel</li><li>• 2821 to 5000ft = Large Wooden Reel</li></ul>

## Agency Approvals

<b>UL Listed File #</b>	E247880,E70148,E118830
<b>UL Recognized File #</b>	E69976
<b>UL Hazardous File #</b>	none
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>