

SE3-SW5U Cut Sheet



STRIDE industrial unmanaged Ethernet switch, 5 ports, (5) Ethernet 10/100Base-T (RJ45) port(s), -10 to +65 deg C, metal housing, IP30, 35mm DIN rail or panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SE3-SW5U>

Technical Specifications

Brand	STRIDE
Item	Ethernet switch
Grade	Industrial
Switch Type	Unmanaged
Number of Ports	5
Communication Port and Connection Type(s)	(5) Ethernet 10/100Base-T (RJ45)
Port Speed(s)	10/100 Mbps auto-detect
Nominal Input Voltage	12-48 VDC
Operating Temperature	-10 to +65 deg C
Housing Material	Metal
IP Rating	IP30
Mounting	35mm DIN rail or panel

Agency Approvals

UL Listed File #	E157382
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SE3-SW5U.pdf>
See store item page for other formats.