

PMP23-CAAN1NF3CJ Cut Sheet



Endress+Hauser Cerabar pressure transmitter, 0 to 90 psig range, +/- 0.3% accuracy, stainless steel sensing element, Output: 4-20 mA, Output 2: IO-Link, 1-1/2in sanitary tri-clamp process connection, 18 to 30 VDC operating voltage, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PMP23-CAAN1NF3CJ>

Technical Specifications

Brand	Endress+Hauser
Item	Pressure transmitter
Series	Cerabar
Pressure Range	0 to 90 psig
Accuracy	+/- 0.3% of full range
Sensing Element Material	Stainless steel
Output	4-20 mA
Output 2	IO-Link
Process Connection	1-1/2in sanitary tri-clamp

Communication Port and Connection Type(s)	(1) 4-pin M12 A-coded (IO-Link)
Port Protocol(s)	IO-Link Class A Device
Port Speed(s)	IO-Link COM2
IO-Link Version	IO-Link SSP Ed.2 v1.1
Operating Voltage	18 to 30 VDC
Electrical Connection	4-pin M12 quick-disconnect
Media Type	Liquid and gases
Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	053988_C_000
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/PMP23-CAAN1NF3CJ.pdf>
See store item page for other formats.