

SE3-SWP2A5U-T Cut Sheet



STRIDE industrial unmanaged PoE+ switch, IEEE 802.3af/at, 120W, 5 ports, (4) PoE+ 10/100Base-T (RJ45) and (1) Ethernet 10/100Base-T (RJ45) port(s), 12-36 VDC nominal input, -40 to +75 deg C, NEMA TS2, 35mm DIN rail or panel mount, hazardous location rated.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SE3-SWP2A5U-T>

Technical Specifications

Brand	STRIDE
Item	PoE+ switch
Grade	Industrial
Switch Type	Unmanaged
PoE Standard	IEEE 802.3af/at
Maximum PoE Output Power	120W
Maximum PoE Output Power per Port	30W
Number of Ports	5
Communication Port and Connection Type(s)	<ul style="list-style-type: none">• (4) PoE+ 10/100Base-T (RJ45)• (1) Ethernet 10/100Base-T (RJ45)
Port Speed(s)	10/100 Mbps auto-detect
Nominal Input Voltage	12-36 VDC
Number of Output Points	1

Nominal Output Voltage	24 VDC
Relay Configuration	(1) Form A (SPST) relay
Number of Isolated Commons	1
Number of Points per Common	1
Load Current	1A/point
Operating Temperature	-40 to +75 deg C
Housing Material	Metal
IP Rating	IP30
NEMA Rating	TS2
Mounting	35mm DIN rail or panel
Additional Information	Capable of being powered by 12-52 VDC while still providing 48-52 VDC required by the PoE standard.
Application	Hazardous location rated

Agency Approvals

UL Listed File #	E157382
UL Recognized File #	None
UL Hazardous File #	ANSI/ISA 12.12.01
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document