

SEP1-SW5UG-1P-T Cut Sheet



STRIDE PRO industrial unmanaged+ Ethernet switch, 5 ports, (4) Ethernet Gigabit (RJ45) and (1) SFP combo Gigabit port(s), -40 to +75 °C, metal housing, IP30, 35mm DIN rail or panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SEP1-SW5UG-1P-T>

Technical Specifications

Brand	STRIDE PRO	Redundant Input Power	Yes
Item	Ethernet switch	Nominal Input Voltage	12-48 VDC
Grade	Industrial	Number of Output Points	1
Switch Type	Unmanaged+	Nominal Output Voltage	24 VDC
Number of Ports	5	Relay Configuration	(1) Form A (SPST) relay
Communication Port and Connection Type(s)	• (4) Ethernet Gigabit (RJ45) • (1) SFP combo Gigabit	Number of Isolated Commons	1
Communication Standard(s)	• IEEE 802.3 10Base-T • IEEE 802.3u 100Base-TX/FX • IEEE 802.3ab 1000Base-T • IEEE 802.3z 1000Base-X • IEEE 802.3z 1000Base-SX/LX • IEEE 802.3x Flow Control • IEEE 802.1p QoS • IEEE 802.1q VLAN Tagging • IEEE 802.3 Internet Group Managing Protocol (IGMP) Snooping • IEEE 802.1D Broadcast Storm Protection (BSP)	Number of Points per Common	1
Port Speed(s)	10/100/1000 Mbps auto-detect	Load Current	1A/point
		Operating Temperature	-40 to +75 °C
		Housing Material	Metal
		IP Rating	IP30
		Mounting	35mm DIN rail or panel
		Additional Information	Port alarm and port mirroring. Optional SFP modules sold separately

Agency Approvals

UL Listed File #	E157382
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SEP1-SW5UG-1P-T.pdf>
See store item page for other formats.