PSB48-120S Cut Sheet





RHINO SELECT PSB series switching power supply, 48 VDC @ 2.5A/120W (adjustable), 120/240 VAC or 120-375 VDC nominal input, 1-phase, enclosed, aluminum housing, 35mm DIN rail mount, removable screw terminal, hazardous location rated.

For complete product information, please see this item on our store at the following link:



https://www.automationdirect.com/pn/PSB48-120S

Technical Specifications

•	
Brand	RHINO SELECT
Item	Power supply
Series	PSB
Power Supply Type	Switching
Efficiency	90% @115 VAC, 91% @230 VAC
Output Configuration	Single output
Output	48 VDC @ 2.5A/120W (adjustable)
Output Voltage Range	48-56 VDC
Input voltage range	85-264 VAC/120-375 VDC
Number of Input Phases	1
Protection Type(s)	 overvoltage short circuit overload

Remote On/Off	No
Voltage Monitoring	Yes
Enclosure Type	Enclosed
Housing Material	Aluminum
IP Rating	IP20
Mounting	35mm DIN rail
Connector Type	Removable screw terminal
NEC Class 2	No
Integrated UPS Battery Control	No
Operating Temperature	-25 to 80 deg C
Application	Hazardous location rated

Agency Approvals

UL Listed File #	E197592
UL Recognized File #	E198298
UL Hazardous File #	None
CE	View CE declarations
CSA File #	249074
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link: https://cdn.automationdirect.com /static/drawings/PSB48-120S.pdf See store item page for other formats.