

# SFC516KC38-10 Cut Sheet



Minerallac hammer-on flange clamp conduit hanger assembly, spring clip, back mount, 25 lbs, UL Type UL 2239. Package of 10. For use with 5/16 to 1/2in flanges and 3/8in conduit.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SFC516KC38-10>

## Technical Specifications

|                          |                         |
|--------------------------|-------------------------|
| Brand                    | Minerallac              |
| Item                     | Conduit hanger assembly |
| Mount Type               | Hammer-on flange clamp  |
| Hanger Type              | Spring clip             |
| Mount Side               | Back                    |
| Material                 | Spring steel            |
| Finish                   | Zinc phosphate plated   |
| Minimum Flange Thickness | 5/16in                  |
| Maximum Flange Thickness | 1/2in                   |
| Load Rating              | 25 lbs                  |
| Outside Diameter         | 0.51in                  |
| Tubing Size              | 1/2in                   |

|                                                       |                                         |
|-------------------------------------------------------|-----------------------------------------|
| Rigid Metallic Conduit (RMC) Trade Size               | 3/8in                                   |
| Electrical Metallic Tubing (EMT) Trade Size           | 3/8in                                   |
| Intermediate Metallic Conduit (IMC) Trade Size        | 3/8in                                   |
| Liquid-tight Flexible Metal Conduit (LFMC) Trade Size | 3/8in                                   |
| UL Type                                               | UL 2239                                 |
| Quantity per Pack                                     | 10                                      |
| For Use With                                          | 5/16 to 1/2in flanges and 3/8in conduit |

## Agency Approvals

|                  |                                        |
|------------------|----------------------------------------|
| UL Listed File # | E165884                                |
| CE               | None                                   |
| CSA File #       | None                                   |
| RoHS Status      | No                                     |
| EU REACH         | <a href="#">View EU REACH document</a> |