

# PSB60-REM20S Cut Sheet



RHINO redundancy module, 2 inputs, 24/48 VDC nominal input, 24-48 VDC output, 20A, alarm contact for operation monitoring, screw terminals, hazardous location rated. Requires (2) matched 24 or 48 VDC power supplies.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PSB60-REM20S>

## Technical Specifications

Brand	RHINO
Item	Redundancy module
Number of Inputs	2
Nominal Input Voltage	24/48 VDC
Input voltage range	24-48 VDC
Nominal Output Voltage	24/48 VDC
Output Voltage Range	24-48 VDC
Amperage Rating	20A
Protection Type(s)	overcurrent

Alarm Contact for Operation Monitoring	Yes
Active Current Sharing	No
Housing Material	Metal
Mounting	35mm DIN rail
Connector Type	Screw terminals
Application	Hazardous location rated
Requires	(2) matched 24 or 48 VDC power supplies

## Agency Approvals

UL Listed File #	None
UL Recognized File #	E198298 & E197592
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	249074
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/PSB60-REM20S.pdf>  
See store item page for other formats.