

SHDS-66C-28.57-28.57 Cut Sheet



Sung-II Machinery drive coupling, high torque disc, 7075-T6 aluminum alloy, clamp, size 66, 1-1/8 x 1-1/8in bore.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SHDS-66C-28.57-28.57>

Technical Specifications

Brand	Sung-II Machinery
Item	Drive coupling
Coupling Type	High torque disc
Material	7075-T6 aluminum alloy
Rated Torque	60 N·m
Maximum Torque	120 N·m
Maximum Angular Misalignment	0.7 degrees
Maximum Parallel Misalignment	0.02mm
Maximum RPM	6500

Attachment Style	Clamp
Coupling Size	66
Overall Length	56.5mm
Bore Diameter	1-1/8in
Bore Diameter 2	1-1/8in
Outside Diameter	66mm
Clamp Screw Fastening Torque	13 N·m
Clamp Screw Size	M6-1.0 x 20mm

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SHDS-66C-28.57-28.57.pdf>
See store item page for other formats.