

# PSH-BCM360S Cut Sheet



RHINO battery control module, 2 inputs, 24/48 VDC nominal input, 23-27 VDC / 47-55 VDC output, 15A at 24 VDC, 7.5A at 48 VDC, alarm contact for operation monitoring, screw terminals. Requires power supply, 12V battery (user-supplied).

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PSH-BCM360S>

## Technical Specifications

<b>Brand</b>	RHINO
<b>Item</b>	Battery control module
<b>Number of Inputs</b>	2
<b>Nominal Input Voltage</b>	24/48 VDC
<b>Input voltage range</b>	24-28 VDC / 48-56 VDC
<b>Nominal Output Voltage</b>	24/48 VDC
<b>Output Voltage Range</b>	23-27 VDC / 47-55 VDC
<b>Amperage Rating</b>	15A at 24 VDC, 7.5A at 48 VDC
<b>Protection Type(s)</b>	<ul style="list-style-type: none"><li>• overvoltage</li><li>• overcurrent</li><li>• battery overcharge</li><li>• reverse polarity</li></ul>

<b>Indicating Type</b>	Single color LED for status indication and (3) output signals
<b>Alarm Contact for Operation Monitoring</b>	Yes
<b>Remote On/Off</b>	Yes
<b>Housing Material</b>	Metal
<b>Mounting</b>	35mm DIN rail
<b>Connector Type</b>	Screw terminals
<b>Requires</b>	Power supply, 12V battery (user-supplied)

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	229285
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/PSH-BCM360S.pdf>  
See store item page for other formats.