

SHR-29C-8-12 Cut Sheet



Sung-II Machinery drive coupling, servo high gain, aluminum alloy, clamp, size 29, 8 x 12mm bore.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SHR-29C-8-12>

Technical Specifications

Brand	Sung-II Machinery
Item	Drive coupling
Coupling Type	Servo high gain
Material	Aluminum alloy
Rated Torque	5.7 N-m
Maximum Torque	11.4 N-m
Maximum Angular Misalignment	1.5 degrees
Maximum Parallel Misalignment	0.2mm

Maximum RPM	21000
Attachment Style	Clamp
Coupling Size	29
Bore Diameter	8mm
Bore Diameter 2	12mm
Outside Diameter	28.8mm
Clamp Screw Fastening Torque	1.8 N-m
Clamp Screw Size	M3

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SHR-29C-8-12.pdf>
See store item page for other formats.