

SHR-43C-19-19 Cut Sheet



Sung-II Machinery drive coupling, servo high gain, aluminum alloy, clamp, size 43, 19 x 19mm bore.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SHR-43C-19-19>

Technical Specifications

Brand	Sung-II Machinery	Maximum RPM	14000
Item	Drive coupling	Attachment Style	Clamp
Coupling Type	Servo high gain	Coupling Size	43
Material	Aluminum alloy	Bore Diameter	19mm
Rated Torque	16 N-m	Bore Diameter 2	19mm
Maximum Torque	32 N-m	Outside Diameter	42.8mm
Maximum Angular Misalignment	1.5 degrees	Clamp Screw Fastening Torque	3.7 N-m
Maximum Parallel Misalignment	0.2mm	Clamp Screw Size	M4

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SHR-43C-19-19.pdf>
See store item page for other formats.