


# Q0140-1 Cut Sheet



Quabbin control and signal cable, unshielded, 2 conductors, 18 AWG, 16-stranded, tinned copper, PVC conductor insulation material, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/Q0140-1>

## Technical Specifications

<b>Brand</b>	Quabbin
<b>Item</b>	Cable
<b>Wire/Cable Type</b>	Control and signal
<b>UL Wire/Cable Type</b>	PLTC, ITC and AWM
<b>Applicable Standards</b>	UL 2464
<b>Application</b>	General purpose
<b>Flexibility</b>	Semi-flexible
<b>Voltage Rating</b>	300V
<b>Conductors</b>	2 conductors
<b>Conductor Size</b>	18 AWG
<b>Conductor Stranding</b>	16-stranded
<b>Conductor Material</b>	Tinned copper
<b>Conductor Insulation Material</b>	PVC
<b>Conductor Insulation Color</b>	Black and red

<b>Shielding</b>	Unshielded
<b>Jacket Material</b>	PVC
<b>Jacket Color</b>	Gray
<b>Nominal Overall Cable Diameter</b>	0.23in
<b>Bulk Length</b>	Cut to length
<b>Package Type</b>	1 to 99ft = Coil, 100 to 678ft = 14 x 7in Reel, 679 to 741ft = 14 x 10in Reel, 742 to 1059ft = 16 x 10in Reel, 1060 to 1638ft = 18 x 10in Reel, 1639 to 2307ft = 18 x 13in Reel, 2308 to 2999ft = 24 x 17in Wooden Reel, 3000 to 6441ft = 30 x 17in Wooden Reel, 6442 to MAX = Large Wooden Reel

## Agency Approvals

<b>UL Listed File #</b>	E66965
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	LL66965
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>