


Q2067-1 Cut Sheet



Quabbin Datamax Cat6 Ethernet cable, shielded, 4 twisted pairs, 26 AWG, 7-stranded, tinned copper, foamed FEP conductor insulation material, PVC jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/Q2067-1>

Technical Specifications

Brand	Quabbin
Item	Cable
Series	Datamax
Protocol	Ethernet
Wire/Cable Type	Cat6 Ethernet
UL Wire/Cable Type	CMP
Applicable Standards	MIL-spec
Application	Data
Flexibility	Semi-flexible
Voltage Rating	300V
Conductors	4 twisted pairs
Conductor Size	26 AWG
Conductor Stranding	7-stranded
Conductor Material	Tinned copper
Conductor Insulation Material	Foamed FEP

Conductor Insulation Color	Pair 1: natural, orange, pair 2: gray, brown, pair 3: natural, green and pair 4: gray, blue
Shielding	Shielded
Jacket Material	PVC
Jacket Color	Black
Nominal Overall Cable Diameter	0.223in
Bulk Length	Cut to length
Package Type	1 to 99ft = Coil, 100 to 785ft = 14 x 7in Reel, 786 to 1120ft = 14 x 10in Reel, 1121 to 1720ft = 16 x 10in Reel, 1721 to 2400ft = 18 x 10in Reel, 2401 to 3120ft = 18 x 13in Reel, 3121 to 6985ft = 24 x 17in Wooden Reel, 6986 to 10000ft = 30 x 17in Wooden Reel

Agency Approvals

UL Listed File #	ETL 3185754
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement