


Q2206-1 Cut Sheet



Quabbin Datamax Cat6e Ethernet cable, unshielded, 4 twisted pairs, 24 AWG, 7-stranded, tinned copper, polyethylene conductor insulation material, PVC jacket, blue, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/Q2206-1>

Technical Specifications

Brand	Quabbin
Item	Cable
Series	Datamax
Protocol	Ethernet
Wire/Cable Type	Cat6e Ethernet
UL Wire/Cable Type	CMR and CMG
Application	Data
Flexibility	Semi-flexible
Voltage Rating	300V
Conductors	4 twisted pairs
Conductor Size	24 AWG
Conductor Stranding	7-stranded
Conductor Material	Tinned copper
Conductor Insulation Material	Polyethylene

Conductor Insulation Color	Pair 1: blue, white/blue, Pair 2: orange, white/orange, Pair 3: green, white/green and Pair 4: brown, white/brown
Shielding	Unshielded
Jacket Material	PVC
Jacket Color	Blue
Nominal Overall Cable Diameter	0.22in
Bulk Length	Cut to length
Package Type	1 to 75ft = Coil, 76 to 805ft = 14 x 7in Reel, 806 to 1150ft = 14 x 10in Reel, 1151 to 1765ft = 16 x 10in Reel, 1766 to 2465ft = 18 x 10in Reel, 2466 to 2500ft = 18 x 13in Reel

Agency Approvals

UL Listed File #	E118830
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	LL51726
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement